



Topcon Retinal 50X Fundus Camera

Reconditioned, calibrated and patient ready.



Topcon 50X Mydriatic Retinal Camera

For increased diagnostic interpretation, three angles of coverage can be easily changed to 50

degrees maximum, 35 degrees, and 20 degrees by a simple lever operation.

Retinal photographs of the peripheries can be taken because the induced distortion can be corrected with the TOPCON developed astigmatic correction device. Controlled illumination settings are available for both normal color photography and fluorescein photography. This unit can be upgraded to a complete digital back end.

FEATURES

- TRC-50X Optical Head
- Power Supply
- One MT-2 Camera back
- Chin rest assembly
- External fixation device
- System is complete and in excellent working condition
- Ideal camera for Digital System Adaptation

For a Bigger Return on Your Investment

Call, text, WhatsApp: 949-362-1150

info@usedeyeequipment.com